For the Pharma/Food Processing Industries - Manual Filter Shaker

.The name to vacuum with

CD-EX Models Certified for:

CLEANING MACHINES For Hazardous Locations (Classes C1618 01 & C1618 81)

Division 1, Class I, Group D and Class II, Groups F and G, T3C *Division 1, Class II Group E (metal dust) motor and switch available* 

Division 2, Class I Group D and Class II, Groups F and G, T3C

CD EX Series **IECEx** 3rd Party Certified Ex d IIB T4 Gb Ex t IIIC T135°C Db IP65 IECEx I CI 10 0040 X



IECEx LCI 10.0040 X Certified for providing an Equipment Protection Level of EPL Db and EPL Gb



**GUARANTEED** for the Safe Recovery of Combustible/Conductive Dusts

**ESD Safe** Vacuum Systems for Hazardous Locations are designed to prevent ignition hazards. We use metal parts or Static Dissipative Powder Coating to prevent Electrostatic Discharge (ESD)



Complies with NFPA 77 "Recommended Practice on Static Electricity"



## Characteristics ULPA **HEP** Pharma Continuous ULPA - Included HEPA Filte Cleanroom EX Certified Available Applications Compatible Duty HEPA - Optional AISI 304 Dry Recovery Detachable SS 304 Less than 10 Tank ohms

- Legally certified explosion proof/dust ignition proof
- Less than 10 ohms of resistivity
- Continuous duty single phase or 3-phase (TEFC) explosion proof/dust ignition proof motor
- ULPA filter with an efficiency of 99.999% at 0.12 micron. Filtration efficiency of 99.9995% at 0.18 micron. Tested IEST-RP-CC001. U15 by MPPS method as per EN 1822. All of our ULPA vacuum systems are aerosol leak tested before leaving our facility - included
- HEPA filter with an efficiency of 99.995% at 0.3 micron. Tested IEST-RP-CC001. H14 by MPPS method as per EN 1822 and OSHA compliant. All of our HEPA vacuum systems are aerosol leak tested before leaving our facility - included
- Muffler assembly, made of stainless steel with sound insulating foam to ensure quiet operation, is included
- Cleanroom compatible with ISO Class 4 (former Class 10). Can be used in the Pharmaceutical industry
- Manual Filter Shaker (MFS) system
- Static dissipative washable main filter is contained within a removable filter chamber
- All stainless steel Type 304 construction
- Detachable recovery tank (DT) for easy disposal of recovered materials
- Static dissipative poly liner and clip for the easy and safe disposal of recovered materials - available

Tel: 1-800-668-4437 (954-925-3625) Fax: 1-800-668-4439 (954-925-3626)

Website: http://www.tiger-vac.com Email: sales@tiger-vac.com

Tiger-Vac Inc. 11 SW 12th Ave #112 Dania, FL 33004 USA **Tiger-Vac International Inc.** 2020 Dagenais Blvd. Ouest Laval, Quebec Canada H7L 5W2

CD/EUR-36L EX DT (MFS) ULPA WITH SS CART Brochure - Downloaded: July 5, 2024 - Page 1/5

- Vertical mounting for areas with space constraints
- Equipped with a Carriage with Suspended Motor Top (CSMT) and tool basket. Includes static dissipative wheels
- Optional Ø1.5" (Ø38 mm) or Ø2" (Ø50 mm) tools & accessories
- Motor and switch for use in the presence of conductive metal dust is available. North-America: Class II, Group E Europe: Dust Group IIIC
- Other motor performances available

## Specifications

CD/EUR-36L						
EX DT (MFS)	112147A1-SS	112147A2-SS	112147A5-SS	112148A3-SS	112149A3-SS	112150A1-SS
ULPA WITH SS CART						
33 CART	CD/EUR-36L EX	CD/EUR-36L EX	CD/EUR-36L EX	CD/EUR-36L EX	CD/EUR-36L EX	CD/EUR-36L EX
	DT (MFS) ULPA WITH SS CART -	DT (MFS) ULPA WITH SS CART -	DT (MFS) ULPA WITH SS CART -	DT (MFS) ULPA WITH SS CART	DT (MFS) ULPA WITH SS CART	DT (MFS) ULPA WITH SS CART
Model Name	CLASS I - GROUP	CLASS I - GROUP	CLASS I - GROUP	CLASS I - GROUP	CLASS I - GROUP	CLASS I - GROUP
	D, CLASS II - GROUPS F & G	D, CLASS II - GROUPS F & G	D, CLASS II - GROUPS F & G	D, CLASS II - GROUPS F & G	D, CLASS II - GROUPS E, F & G	D, CLASS II - GROUPS E, F & G
Туре	Electric	Electric	Electric	Electric	Electric	Electric
(Powerhead) TEFC Motor	Yes	Yes	Yes	Yes	Yes	Yes
Tension	460 V	230 V	575 V	120 V	120 V	460 V
	400 V 60 Hz	60 Hz	60 Hz	60 Hz	60 Hz	60 Hz
Frequency Phase				Single		
	Three	Three	Three		Single	Three
Wattage	1480 W	1480 W	1480 W	1110 W	1110 W	1480 W
Power	2 HP	2 HP	2 HP	1.5 HP	1.5 HP	2 HP
Amperage	2.6 A	5.2 A	2.1 A	15 A	15 A	2.6 A
Air Flow	158 CFM	158 CFM	158 CFM	125 CFM	125 CFM	158 CFM
Vacuum Pressure	130 " H <sub>2</sub> 0	130 " H <sub>2</sub> 0	130 " H <sub>2</sub> 0	120 " H <sub>2</sub> 0	120 " H <sub>2</sub> 0	130 " H <sub>2</sub> 0
VRV Setting	80 " H <sub>2</sub> 0	80 " H <sub>2</sub> 0	80 " H <sub>2</sub> 0	80 " H <sub>2</sub> 0	80 " H <sub>2</sub> 0	80 " H <sub>2</sub> 0
Sound Level						
when	72 db(A)	72 db(A)	72 db(A)	72 db(A)	72 db(A)	72 db(A)
equipped with Silencer						
Type of Power Outlet	Not Included	Not Included	Not Included	Not Included	Not Included	Not Included
Suction Inlet Port	2 "	2 "	2 "	2 "	2 "	2 "
Cart Type	Detachable Tank (DT)	Detachable Tank (DT)	Detachable Tank (DT)	Detachable Tank (DT)	Detachable Tank (DT)	Detachable Tank (DT)
Filter Cleaning	Manual Filter Shaker (MFS)	Manual Filter Shaker (MFS)	Manual Filter Shaker (MFS)	Manual Filter Shaker (MFS)	Manual Filter Shaker (MFS)	Manual Filter Shaker (MFS)
Dust Recovery Tank	9.5 Gal	9.5 Gal	9.5 Gal	9.5 Gal	9.5 Gal	9.5 Gal
Length	30 "	30 "	30 "	30 "	30 "	30 "
Width	24 "	24 "	24 "	24 "	24 "	24 "
Height	75 "	75 "	75 "	75 "	75 "	75 "
Weight						
(Vacuum Only)	249 lb.	249 lb.	249 lb.	249 lb.	249 lb.	249 lb.
Cord Length	50 ft.	50 ft.	50 ft.	50 ft.	50 ft.	50 ft.
Star Shaped						
Main Filter Surface Area	9.25 ft <sup>2</sup>	9.25 ft <sup>2</sup>	9.25 ft <sup>2</sup>	9.25 ft <sup>2</sup>	9.25 ft <sup>2</sup>	9.25 ft <sup>2</sup>
CD/EUR-36L				l		
EX DT (MFS) ULPA WITH	112150A2-SS	112150A5-SS				
SS CART						
	CD/EUR-36L EX DT (MFS) ULPA	CD/EUR-36L EX DT (MFS) ULPA				

Tiger-Vac Inc. 11 SW 12th Ave #112 Dania, FL 33004 USA **Tiger-Vac International Inc.** 2020 Dagenais Blvd. Ouest Laval, Quebec Canada H7L 5W2 Tel: 1-800-668-4437 (954-925-3625) Fax: 1-800-668-4439 (954-925-3626) Website: http://www.tiger-vac.com Email: sales@tiger-vac.com

Model Name	WITH SS CART CLASS I - GROUP D, CLASS II - GROUPS E, F & G	WITH SS CART CLASS I - GROUP D, CLASS II - GROUPS E, F & G	
Type (Powerhead)	Electric	Electric	
TEFC Motor	Yes	Yes	
Tension	230 V	575 V	
Frequency	60 Hz	60 Hz	
Phase	Three	Three	
Wattage	1480 W	1480 W	
Power	2 HP	2 HP	
Amperage	5.2 A	2.1 A	
Air Flow	158 CFM	158 CFM	
Vacuum Pressure	130 " H <sub>2</sub> 0	130 " H <sub>2</sub> 0	
VRV Setting	80 " H <sub>2</sub> 0	80 " H <sub>2</sub> 0	
Sound Level when equipped with Silencer	72 db(A)	72 db(A)	
Type of Power Outlet	Not Included	Not Included	
Suction Inlet Port	2 "	2 "	
Cart Type	Detachable Tank (DT)	Detachable Tank (DT)	
Filter Cleaning	Manual Filter Shaker (MFS)	Manual Filter Shaker (MFS)	
Dust Recovery Tank	9.5 Gal	9.5 Gal	
Length	30 "	30 "	
Width	24 "	24 "	
Height	75 "	75 "	
Weight (Vacuum Only)	249 lb.	249 lb.	
Cord Length	50 ft.	50 ft.	
Star Shaped Main Filter Surface Area	9.25 ft <sup>2</sup>	9.25 ft <sup>2</sup>	

Please note that specifications are subject to change without notice

## Use only recommended tools & accessories



**ULPA Filter - Included** 

Internal (upstream) HEPA filter No. 219212 - Optional



Conductive Star Shaped Filter with Cage - Included



Ø1.5" (Ø38 mm) Static Dissipative Tools and Accessories - Optional



Ø2" (Ø50 mm) Static Dissipative Tools and Accessories - Optional



CD/EUR-36L EX DT (MFS) ULPA SS with Recovery Tank and Filter Chamber removed