

Applicable Requirements: ANSI/UL 1017 CSA C22.2 No.243



Characteristics













Applications

Cleanroom Compatible

Wet and Dry

Efficiency Unit

Dissipating



Accessories



Less than 10



- ULPA filter with an efficiency of 99.999% at 0.12 micron. Filtration efficiency of 99.9995% at 0.18 micron. Tested IEST-RP-CC001. U15 by MPPS method as per EN 1822. All of our ULPA vacuum systems are aerosol leak tested before leaving our facility - included
- Cleanroom compatible with ISO Class 4 (former Class 10). Can be used in the Pharmaceutical industry
- Static free and ESD safe
- EMI/RFI Shielded
- 5-stage filtration system, includes dual ULPA filters (U15) (one for the working air and one for the cooling air), double cloth filter, and disposable filter bags
- Designed for use in contamination controlled environments
- Heavy duty 2-stage by-pass motor
- For wet & dry recovery
- Stainless steel recovery tank
- Mounted on a 4-wheel dolly for easy maneuverability
- Includes a complete tool kit.
- Cable Hook Holder Included
- Drain Valve Assembly Optional

Specifications

CWR-8 (4W)	110491A
Model Name	CWR-8 (4W)
Type (Powerhead)	Electric
Tension	120 V
Frequency	60 Hz
Phase	Single
Wattage	1200 W
Power	1.6 HP
Amperage	10.5 A
Air Flow	110 CFM
Vacuum Pressure	107 " H ₂ 0
Sound Level	75 dB(A)
Type of Power Outlet	120V
Suction Inlet Port	1.5 "
Cart Type	4 Wheel Dolly (4W)
Filter Cleaning	None
Dust Recovery Tank	6.5 Gal
Dry Recovery - Disposable Filter Bag	2.5 gal.
Liquid Recovery Capacity	6.5 gal.
Length	23 "
Width	19 "
Height	30 "
Weight (Vacuum Only)	50 lb.
Cord Length	35 ft.

Please note that specifications are subject to change without notice

Use only recommended tools & accessories



ULPA Filter - Included



Autoclavable Suction Hose and Accessories - Optional



CWR Tools and Accessories - Included



CWR-8 (4W) Cable Holder Hook - Included

Tel: 1-800-668-4437 (954-925-3625) Fax: 1-800-668-4439 (954-925-3626) Website: http://www.tiger-vac.com Email: sales@tiger-vac.com