CD-120V EX PHARMA SERIES

Pharma - Dry Recovery Only



CD-EX Models Certified for:

CLEANING MACHINES For Hazardous Locations (Classes C1618 01 & C1618 81)

Division 1, Class I, Group D and Class II, Groups F and G, T3C Division 1, Class II Group E (metal dust) motor and switch

Division 2, Class I Group D and Class II, Groups F and G, T3C

CD EX Series IECEx 3rd Party Certified

Ex d IIB T4 Gb

Ext IIIC T135°C Db IP65

IECEx LCI 10.0040 X

Certified for providing an Equipment Protection Level of EPL Db and EPL Gb



GUARANTEED for the Safe Recovery of Combustible/Conductive

ESD Safe Vacuum Systems for Hazardous Locations are designed to prevent ignition hazards.

We use metal parts or Static Dissipative Powder Coating to prevent Electrostatic Discharge (ESD)



Complies with NFPA 77 "Recommended Practice on Static Electricity'



Characteristics















Duty

ohms

- Legally certified explosion proof/dust ignition proof
- Less than 10 ohms of resistivity
- ULPA filter with an efficiency of 99.999% at 0.12 micron. Filtration efficiency of 99.9995% at 0.18 micron. Tested IEST-RP-CC001. U15 by MPPS method as per EN 1822. All of our ULPA vacuum systems are aerosol leak tested before leaving our facility - included
- Includes a muffler for noise reduction
- Available with a Conductive Filter Bag (CFB) or Manual Reverse Purge with Filter Tubes (MRPFT) system
- Designed to be attached to process machines and for general cleanup
- Can also be used for the recovery of tablets in the Pharmaceutical industry
- Continuous duty single phase (TEFC) explosion proof/dust ignition proof motor
- For dry recovery only
- All stainless steel Type 304 construction
- Vertical mounting for areas with space constraints
- Static dissipative poly liner and retainer clip for the easy and safe disposal of recovered materials included
- Includes a complete static dissipative tool kit
- Motor and switch for use in the presence of conductive metal dust is available. North-America:

Class II, Group E Europe: Dust Group IIIC

• Other motor performances available

Specifications

CD-120V EX PHARMA SERIES	112163A3	112176A3
Model Name	CD-120V EX (CFB) PHARMA - CLASS I - GROUP D, CLASS II - GROUPS F & G	CD-120V EX (MRPFT) PHARMA - CLASS I - GROUP D, CLASS II - GROUPS F & G
Type (Powerhead)	Electric	Electric
TEFC Motor	Yes	Yes
Tension	120 V	120 V
Frequency	60 Hz	60 Hz
Phase	Single	Single
Wattage	750 W	750 W
Power	1 HP	1 HP
Amperage	13.5 A	13.5 A
Air Flow	110 CFM	110 CFM
Vacuum Pressure	110 " H ₂ 0	110 " H ₂ 0
VRV Setting	65 " H ₂ 0	65 " H ₂ 0
Sound Level	68 dB(A)	68 dB(A)
Type of Power Outlet	Not Included	Not Included
Suction Inlet Port	2 "	2 "
Cart Type	Carriage Base (CB)	Carriage Base (CB)
Filter Cleaning	Conductive Filter Bag (CFB)	Manual Reverse Purge with Filter Tubes (MRPFT)
Dust Recovery Tank	13.2 Gal	13.2 Gal
Length	27 "	27 "
Width	19 "	19 "
Height	59 "	59.5 "
Weight (Vacuum Only)	211 lb.	214 lb.
Cord Length	50 ft.	50 ft.

Please note that specifications are subject to change without notice

Use only recommended tools & accessories



Filter Tubes Assembly for MRPFT models - Included





CD-120V EX (CFB) PHARMA



CD-120V/230V Tool Kit - Included

Tel: 1-800-668-4437 (954-925-3625) Fax: 1-800-668-4439 (954-925-3626) Website: http://www.tiger-vac.com Email: sales@tiger-vac.com