Dry Recovery Only



NFPA'77

Applicable Requirements : ANSI/UL 1017 CSA C22.2 No.243

Complies with NFPA 77 "Recommended Practice on Static Electricity"



Characteristics



- Ideal for housekeeping and general cleaning
- Complies with NFPA 652 paragraph 8.4.2.2.1.7 and NFPA 654 paragraph 8.4.3.7 (1) to (7)
- Protected against ingress of dust
- HEPA filter with an efficiency of 99.995% at 0.3 micron. Tested IEST-RP-CC001. H14 by MPPS method as per EN 1822 and OSHA compliant. All of our HEPA vacuum systems are aerosol leak tested before leaving our facility - included
- Heavy duty 2-stage by-pass motor
- Longer life brushless motor available. Always with 2 x H14 HEPA filters
- For dry recovery only
- A package of the disposable conductive "wet" recovery bags is included with the vacuum cleaner
- Stainless steel tank Type 430 fits any application
- Filter blockage indicator light
- Includes a complete static dissipative tool kit

Specifications

| 2D-10 (4W) HEPA ORDLOC-652 | 113185A | 113185A-BLSD |
|---|----------------------------|---|
| Model Name | 2D-10 (4W) HEPA ORDLOC-652 | 2D-10 (4W) HEPA ORDLOC-652 W/BRUSHLESS MOTOR |
| Type (Powerhead) | Electric | Electric |
| Tension | 120 V | 120 V |
| Frequency | 60 Hz | 60 Hz |
| Phase | Single | Single |
| Wattage | 1207 W | 1100 W |
| Power | 1.6 HP | 1.5 HP |
| Amperage | 10.5 A | 13 A |
| Air Flow | 110 CFM | 127 CFM |
| Vacuum Pressure | 107 " H ₂ 0 | 89 " H ₂ 0 |
| Sound Level | 75 dB(A) | 75 dB(A) |
| Type of Power Outlet | 120V | 120V |
| Suction Inlet Port | 60 mm | 60 mm |
| Cart Type | 4 Wheel Dolly (4W) | 4 Wheel Dolly (4W) |
| Dry Recovery - Disposable Filter Bag | 5 gal. | 5 gal. |
| Length | 17 " | 17 " |
| Width | 17 " | 17 " |
| Height | 34 " | 35 " |
| Cord Length | 35 ft. | 35 ft. |

Please note that specifications are subject to change without notice

Use only recommended tools & accessories



Upstream HEPA Filter - Included



Static Conductive Toolkit - Included



Conductive Recovery Bags - included



Longer Life Brushless Motor Available (always with 2 x H14 HEPA filters)