

Applicable Requirements: ANSI/UL 1017 CSA C22.2 No.243



Characteristics













Dissipating





Applications

Compatible

316

High Filtration



Efficiency Unit

EMI Shielded ohms

- ULPA filter with an efficiency of 99.999% at 0.12 micron. Filtration efficiency of 99.9995% at 0.18 micron. Tested IEST-RP-CC001. U15 by MPPS method as per EN 1822. All of our ULPA vacuum systems are aerosol leak tested before leaving our facility - included
- HEPA filter with an efficiency of 99.995% at 0.3 micron. Tested IEST-RP-CC001. H14 by MPPS method as per EN 1822 and OSHA compliant. All of our HEPA vacuum systems are aerosol leak tested before leaving our facility - included
- Cleanroom compatible with ISO Class 4 (former Class 10). Can be used in the Pharmaceutical industry
- Static free and ESD safe
- EMI/RFI Shielded
- TELECOM package available
- 5-stage filtration system, includes an ULPA filter (U15), HEPA filter (H14), PTFE laminated main cloth filter, safety filter, and disposable filter bags
- Designed for use in contamination controlled environments
- Powerful dual speed Thru-Flow motor
- For dry recovery only
- Autoclavable stainless steel Type 316 filter chamber and wheel base
- Safe containment canister for the safe collection, containment and disposal of potent compounds available
- Mounted on a 4-wheel dolly for easy maneuverability
- 3 optional tool kits Standard, ESD Safe, and Autoclavable


Specifications

EMI-1000 (CV)	110132A
Model Name	EMI-1000 (CV)
Type (Powerhead)	Electric
Tension	120 V
Frequency	60 Hz
Phase	Single
Wattage	1000 W
Power	1.3 HP
Amperage	8.5 A
Air Flow	120 CFM
Vacuum Pressure	95 " H ₂ 0
Sound Level	70 dB(A)
Type of Power Outlet	120V
Suction Inlet Port	1.5 "
Cart Type	4 Wheel Dolly (4W)
Filter Cleaning	None
Containment Canister Recovery Capacity	2 Gal
Length	16 "
Width	16 "
Height	34 "
Weight (Vacuum Only)	36 lb.
Cord Length	35 ft.

Please note that specifications are subject to change without notice

Tel: 1-800-668-4437 (954-925-3625) Website: http://www.tiger-vac.com Fax: 1-800-668-4439 (954-925-3626) Email: sales@tiger-vac.com

Use only recommended tools & accessories



EMI-1000 Air Flow Schematic for Safe Containment Model



Safe containment canister - Included



ULPA Filter - Included



HEPA Filter with Safety Filter - Included



Main Cloth Filter - Included



323600 - Ø1.25" (Ø32 mm) Standard Tools and Accessories (Kit #1) - Optional



323602 - Ø1.25" (Ø32 mm) ESD safe tools and accessories (Kit #323604 - Ø1.25" (Ø32 mm) Autoclavable tools and accessories #2) - Optional (Kit #3) - Optional



Stainless steel holding bracket - Optional