



GUARANTEED for the Safe Recovery of Combustible/Conductive Dusts and Flammable Liquids

Characteristics



Activated Carbon




Corrosive Recovery



Pharma Applications



Cleanroom Compatible



Static Dissipating



SD Accessories - Included



Wear Protective Clothing (PPE)



Wet Recovery



- Static dissipative and grounded
- Cleanroom compatible with ISO Class 4 (former Class 10). Can be used in the Pharmaceutical industry when equipped with stainless steel Type 304 4-wheel dolly or tilting cart
- Designed for the recovery of acids and corrosive liquids
- To be used as a Recovery Unit in conjunction with a vacuum system
- Available with a variety of activated carbon, including KINA 3® activated carbon for the adsorption of chloride and acid vapors (HF, HCL, etc). Other types of activated carbon are available. Carbon cartridges must be ordered separately - not included
- For liquid recovery
- Static dissipative acid resistant polyethylene, nylon and PVC
- Available with a 4-wheel dolly, tilting cart, or hydro-cart
- 4-wheel dolly, and tilting cart available in stainless steel
- Includes a complete static dissipative tool kit

Specifications

ARU-15 EX SERIES	211867	211871	211875	211879
Model Name	ARU-15 EX (TC) MRAC	ARU-15 EX (TC)	ARU-15 EX CR (TC)	ARU-15 EX CR (TC) MRAC
Suction Inlet Port	1.5 "	1.5 "	1.5 "	1.5 "
Cart Type	Tilt Cart (TC)	Tilt Cart (TC)	Tilt Cart (TC)	Tilt Cart (TC)
Filter Cleaning	None	None	None	None
Liquid Recovery Capacity	12.5 gal.	12.5 gal.	12.5 gal.	12.5 gal.

Please note that specifications are subject to change without notice

Use only recommended tools & accessories



ARU EX Tools and Accessories - Included



Liquid Filter - Included



Activated Carbon Cartridge - Optional